



Be Right™



Dönüştürülebilir pH Sensörü, 3/4" kombinasyon pH elektrodu, PPS

Ürün Numarası:

PC1R1A

TRY Fiyat:

Bize Ulaşın

Mevcut

Analog pH sensör, içinden akışlı veya daldırma probu olarak kullanılabilir. Daha sık değişim gerektiren yüksek agresiflik düzeyine sahip prosesler için uygundur. Sıcaklık elemanı olmayan.

PPS, Dönüştürülebilir Gövde Stili, 4,5 m Analog Kablo, Genel Amaçlı Cam pH Elektrot, Pt 1000 Sıcaklık Telafisi

Düşük Fiyat-Mükemmel Performans

These combination sensors are designed for specialty applications for immersion or in-line mounting. The reference cell features a double-junction design for extended service life, and a built-in solution ground. The body is molded from chemically-resistant PPS® or PVDF, and the reference junction is coaxial porous PTFE. All sensors are rated 0 to 105°C up to 100 psig, and have integral 4.5 m (15 ft.) cables with tinned leads. The PC-series (for pH) and RCseries (for ORP) combination sensors are ideal for measuring mild and aggressive media.

Özel Elektrot Yapılandırmaları

Sensors with rugged dome electrodes, “easy-to-clean” flat glass electrodes, and even HF (hydrofluoric acid) resistant glass electrodes are available for a wide variety of process solutions.

Sıcaklık Telafisi Elemanı Seçeneği

The PC-series combination pH sensors are available with or without a PT1000 ohm RTD temperature element. The RC-series combination ORP sensors are supplied without a temperature element.

Çok Yönlü Montaj Tarzları

Sensors are available in three mounting styles—convertible, insertion, and sanitary.

Tam Özellikli Hach SC Dijital Kontrolörler

There are no complicated wiring or set up procedures with any Hach SC controller. Just plug in any combination of Hach digital sensors and it's ready to use—it's “plug and play.” One or multiple sensors—the SC controller family allows you to receive data from up to eight Hach digital sensors in any combination using a single controller.

Teknik özellikler

Akış:	0 - 2 m/s
Basınç aralığı:	100 °C'de 6,9 bar
Doğruluk:	± 0,1 pH referans şartlar altında
Garanti:	6 aylar
Gövde malzemesi:	PPS, General Purpose
İletim mesafesi:	maks. 1000 m HACH dijital gateway,
	terminasyon kutusu ve SC100 kontrolörü ile kullanıldığındá
İşletme sıcaklık aralığı:	0 - 105 °C
Kablo Uzunluğu:	4.5 m çiplak ve kalaylanmış tellerle sonlandırılmış

Malzeme: Sensör: Cam
Ölçüm aralığı: 0 - 14 pH
Parametre: pH
Prob türü: Convertible
Sıcaklık kompanzasyonu: Yes, PT1000