



Filter, versapor 3um 25mm, PK/25

Ürün Numarası:

2594025

TRY Fiyat:
Mevcut

Bize Ulaşın

Designed for rapid, qualitative filtration of particulate matter from aqueous samples using a 25 mm glass fiber filter or other medium with porosity $\geq 1.0 \mu\text{m}$ (micron). Used in Hach Method 10014 for Ultra Low Range Chlorine in Wastewater (EPA Accepted method).

Teknik özellikler

Çap: 25 mm

Hacim / Paket boyutu: 25 pk