



Filter, TSS glass fiber, pore size 1.5 µm, diameter 70 mm, 100/pk

Ürün Numarası:	253053
TRY Fiyat:	Bize Ulaşın
Mevcut	

TSS Filters are recommended for use in Standard Methods 2540 C and 2540 D. Optimized surface characteristics of this binderless borosilicate glass microfiber filter eliminates pin-holing and fiber-shedding to ensure consistent, accurate results. Fast flow rate, fine porosity and 1.5 µm particle retention makes the TSS Filter the preferred choice of environmental chemists for total suspended solids analysis of water and wastewater.

Teknik özellikler

Çap:	70 mm
Gözenek boyutu:	1.5 µm
Hacim / Paket boyutu:	100 /pk
Malzeme:	Glass Microfiber