



EZ9130 Heavy-duty Filtration System for digestate samples, pore size 500 µm, 1 stream

Ürün Numarası: **EZ9130.XX340091**
TRY Fiyat: Bize Ulaşın

Universal self-cleaning filtration for digestate samples - compatible with the EZ7200 Series

About the EZ9100 Series

The successful implementation of online analysers in process control strategies could not have been achieved without the development of a new generation of automatic sampling and sample preconditioning systems. The EZ9100 Series are the result of many years of field experience in combining analysers with filtration units.

Simplified operation by self-cleaning action

All preconditioning systems are designed for fully automatic operation and require virtually no human intervention. Basically all systems are incorporated either with a blow-back action by instrument air, or a specific cleaning cycle. This fundamental design principle does not merely allow trouble-free sampling, moreover it contributes to high up-times.

The EZ9130 is a filtration system developed specifically for sampling wet type anaerobic digesters to make solid-free samples available for online analysis. Devoid of overly complex engineering, the filtration can handle the difficult properties of sludge and wastewaters charged with high levels of insoluble constituents:

- Self-cleaning sample filtration with various pore sizes
- Large-bore pneumatic ball valves for sample and drain
- Automatic cleaning by solenoid controlled instrument air
- PLC or analyser controlled cleaning frequency

Teknik özellikler

Ağırlık:	18 kg
Boyut (Y x G x D):	1150 mm x 750 mm x 200 mm
Cihaz havası:	Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air
Cleaning:	Automatic blowback by solenoid controlled instrument air
Drenaj:	Overflow sample D=50 mm; overflow Static Pressure Regulator 3/8" OD
Enerji:	24 VDC, powered by analyser
Gözenek boyutu:	500 µm

Koruma sınıfı:	IP55
Malzeme:	Filter: SS 316L
	Piping: PVC
	Manual ball valves: PVC
	Tubing: Norprene, PFA, PE
	Panel: weather resistant Trespa
Numune akışı sayısı:	1 stream
	Optional:
	1 to 8 streams
Numune sıcaklığı:	Max. 65 °C
Önemli açıklamalar:	Backflush valve controlled by Analyzer
Önemli özellik:	Heavy Duty (Anasense)
Required fast loop:	2 m/s
Size:	500 µm
Toprak bağlantısı:	Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm ²
Yıkama suyu basıncı:	3/8" BSPF, 4 bar max.