



EZ1016sc Total Hardness Analyser

Ürün Numarası: **EZ1016.XXXXXXXT**
TRY Fiyat: Bize Ulaşın

Online colorimetric analysis of Total Hardness in water

EZ1000 Total Hardness Analysers achieve excellent precision and accuracy. At the heart of the colorimeter there is a compact photometer assembly developed especially for the EZ Series. Consumption of reagents is reduced by low volume analysis, yet high sensitivity is assured by a long optical path length. The limit of detection is in the low µg/L range.

Results you can rely on

Smart automatic features for calibration, validation, priming and cleaning are embedded in the controller software and contribute to analytical performance, maximised uptime and negligible operator intervention. The consumption of reagents is monitored through automatic counters, signalling the need of replacement. Precision micropumps dose all reagents. Sample lines and analysis vessel are cleaned with demineralised water to eliminate cross contamination between samples. Electronic and wet-chemical part of the analyser are strictly separated. A transparent door allows for instant visual inspection of the wet part.

The system has standard Claros connection enabled, which allows for remote monitoring, operating and troubleshooting.

Flexibility that meets your needs

EZ Series Total Hardness Analysers come in an attractive, ergonomic mainframe with a compact footprint. All hardware is controlled by the integrated digital SC controller. The modular build allows for the analyser to match your application and operational needs.

- The standard measuring range can be narrowed by a different calibration range or extended via internal dilution options.
- Analog and digital output options
- Multiple stream analysis for up to 8 sample streams

There are many additional options available. Please contact Hach for more details.

Teknik özellikler

Ağırlık:	25 kg
Akış Hızı:	100 - 300 mL/min
Alarm :	Malfunction, maintenance, analyser busy
Analog çıkışlar:	Active 4 - 20 mA max. 500 Ohm load, standard 1, max. 8 (option)
Boyut (Y x G x D):	690 mm x 465 mm x 330 mm

Cihaz havası:	Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air
Demineralize su:	For rinsing / dilution
Dijital çıkışlar:	Optional: Modbus (TCP/IP, RTU/RS485), Profinet, Profibus DP, Ethernet/IP
Doğrulama:	Automatic; frequency freely programmable
Doğruluk:	Better than 2% full scale range for standard test solutions
Drenaj:	Atmospheric pressure, vented, min. Ø 32 mm
Enerji:	100 - 240 VAC, 50/60 Hz
	Max. power consumption: 120 VA
Garanti:	24 aylar
Girişimler:	Some metal ions interfere by causing fading or indistinct end points or by stoichiometric consumption of EDTA. Large amounts of colour and turbidity interfere. Fats, oil, proteins, surfactants and tar.
Kalibrasyon:	Automatic, 2-point; frequency freely programmable
Koruma sınıfı:	IP44
Malzeme:	Hinged part: Thermoform ABS, door: PMMA
	Wall section: galvanised steel, powder coated
Metot:	Colorimetric
Model:	EZ1016sc
Numune akışı sayısı:	1, 2, 4, or 8
Numune basıncı:	By external overflow vessel
Numune kalitesi:	Maximum particle size 100 µm, < 0.1 g/L; Turbidity < 50 NTU
Numune sıcaklığı:	10 - 30 °C
Ölçüm aralığı:	0,05 - 1 mg/L CaCO ₃
	Optional (with internal dilution):
	0,025 - 0,25 mg/L
	0,025 - 0,5 mg/L
	0,5 - 10 mg/L
	1,25 - 25 mg/L
	2,5 - 50 mg/L
	3,75 - 75 mg/L
	5,0 - 100 mg/L
Ölçüm metodu:	Colorimetric measurement at 610 nm using calmagite/EDTA
Ölçüm süresi:	10 min (dilution + 5 min.)
Ortam sıcaklığı:	10 - 30 °C ± 4 °C deviation at 5 - 95% relative humidity (non-condensing)
Otomatik temizleme:	Evet
Parametre:	Total Hardness
Reaktif gereksinimi:	Keep between 10 - 30 °C
Saptama limiti:	≤ 2.5 µg/L CaCO ₃
Sertifikalar:	CE compliant / ETL certified
Toprak bağlantısı:	Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm ²